

McGill Raynox Table for JVC Everio GZ-MG505

Model	Magnification	Required Adapter	Video Mode		Still Mode		Distance to the Object/ Minimum shooting distance	Effective Zooming without vignetting	Remarks
			16:9	4:3	16:9	4:3			
HD-2200PRO	2.2X	Direct mount	☉	☉	☉	☉	7m	7X - 10X (Video Mode) 7X - 8X (Still Mode)	use at max telephoto position
HD-3031PRO	0.3X	Direct mount	☉	☉	☉	☉	Up to the closest to the lens at most wide position	1X - 6X	When a wide angle lens is used at Telephoto position, make sure the object is under a bright condition
HD-5005PRO	0.5X	RA3737(Included)	☉	☉	▲ (Vignetting)	▲ (Vignetting)	Up to the closest to the lens at most wide position	whole zoom area	
QC-303	0.3X	Direct mount	✘ (Vignetting)	☉	✘ (Vignetting)	✘ (Vignetting)	Up to the closest to the lens at most wide position	1X - 2X	use at max wideangle position
QC-505	0.5X	Direct mount	☉	☉	☉	☉	Up to the closest to the lens at most wide position	1X - 2X	

The focal length of GZ-MG505 : Video mode-3.2mm-32mm(46.2mm-462mm in equivalent in 35mm format) / Still mode-4mm-32mm(43mm-344mm in equivalent in 35mm format)